



The 6C measurement - laboratory experiments and engineering applications

Felix Bernauer (1), Joachim Wassermann (1), Frederic Guattari (2), Elliot de Toldi (2), Klaus G. Hinzen (3), and Heiner Igel (1)

(1) Department of Earth- and Environmental Sciences, Munich University, Theresienstrasse 41, 80333 Muenchen, Germany, (2) iXblue, 34, Rue de la croix de fer, 78100 Saint-Germain-en-Laye, France, (3) Earthquake Geology Division, Cologne University, Vinzenz-Pallotti-Str. 26, 51429 Bergisch Gladbach, Germany

With the development of BlueSeis3A (by iXblue, France, in collaboration with researchers from Ludwig-Maximilians University of Munich, Germany, within the framework of the European Research Council Project, ROMY) field experiments with co-located measurements of 3 components of translational motion and 3 components of rotational motion (6C - measurements) can be carried out. BlueSeis3A has a high sensitivity ($\sim 20 \text{ nrad s}^{-1} \text{ Hz}^{-1/2}$) in a broad frequency range (0.001 Hz to 50 Hz) and thus opens the possibility to investigate the benefit of 6C measurements in a broad range of applications. In this contribution, we first demonstrate in laboratory experiments that directly measured rotational motion makes it possible to correct classical seismometer recordings for the contribution of dynamic tilt and to improve the reconstruction of static displacement as it might occur in the near-field of volcanic long period events. As a second part we show the advantage of directly measured rotational motion for applications in civil engineering. Results from a recent measurement campaign in the Cathedral of Cologne, Germany, show the possibility to directly observe the torsional modes of a structure and to fully reconstruct the time history of a moving point in space with 6 degrees of freedom.